


# INSIDE ARROWS FOR PLATE-SIDE EXCHANGE TYPE

—STANDARD · SHALLOW ARROW MARK TYPE—



**RoHS**

**Inside Arrow**

No.	dh7	B	L	K
3	1.4	2	8	3
4	1.9	2.8	8	3
5	2.3	3.4	8	3
6	2.8	4	8	3
8	4	5.6	10	4
10	5	6.5	12	4
16	10	12	14	6
20	12	14	16	6

No.	Arrow mark depth (mm)	
	Standard	Shallow
3	0.22	—
4	0.25	0.14
5	0.30	0.16
6	0.40	0.18
8	0.40	0.20
10~20	0.50	0.22

Details P.570

Ⓜ SUS420  
Ⓜ 50~53HRC

Ⓢ Inside arrows on this page are adapted for combination with outside rings of date marked pin sets on P.575 · 581, and products on P.578 · 582.

Year Type				No-marking Type			
Indication	Part Number Type	No.	Year	Indication	Part Number Type	No.	U/Price 1~9
Year	DYY DYYU (Shallow arrow) Ⓢ Except for No.3	3	18 for 2018 Ⓢ Days to ship will be 5-days for the adjustment of production after November 2018. It is scheduled to close sales in April 2019.	No-marking	DN DNU (Shallow arrow) Ⓢ Except for No.3	3	Quotation
		4					
		5					
		6					
		8					
		10	19 for 2019 (available from Sept., 2018) Ⓢ Days to ship will be 5-days for the adjustment of production after November 2019. It is scheduled to close sales in April 2020.			4	Quotation
		16	20 for 2020 (available from Sept., 2019) Ⓢ Days to ship will be 5-days for the adjustment of production after November 2020. It is scheduled to close sales in April 2021.			5	
		20				6	
						8	
						10	

**Order**

Part Number — Year  
(Year) DYY6 — 18  
(No-marking) DN10

**Days to Ship**

Quotation

**Price**

Quotation

Character Designation Type			
Indication	Part Number		U/Price 1~9
	Type	No.	
2 characters	DYM	5	Quotation
		6	
		8	
		10	
		16	
		20	

Engraving characters (2 characters · Characters printed in blue in indications)

0	1	2	3	4
5	6	7	8	9

A B C D E J  
F G H I N S T Y  
K L M P Q R V W X Z

Name	Characters for engraving	Order code
Slash	/	¥
Greater	>	>
Less	<	<
Plus	+	+
Minus	-	#
Space	□	%

Ⓢ 2 characters can be engraved on the inside arrow.  
Ⓢ Use ¥ for indicating / (slash), # for — (minus), and % for □ (space).

**Order**

Part Number — Characters for engraving  
DYM10 — AB

**Days to Ship**

Quotation

**Price**

Quotation

# OUTSIDE RINGS FOR PLATE-SIDE EXCHANGE TYPE

Ⓢ Non JIS material definition is listed on P.1351 - 1352

**RoHS**

**Outside Ring**

Dm6	Dh7	dh7	L
3	3	1.4	8
4	4	1.9	8
5	5	2.3	8
6	6	2.8	8
8	8	4	10
10	10	5	12
16	16	10	14
20	20	12	16

Details P.570

Ⓜ SUS420  
Ⓜ 50~53HRC

Ⓢ Outside rings on this page are adapted for combination with inside arrows of date marked pin sets on P.575, and products on P.577.

Year Switching Type				Month · Day · No-marking Type			
Indication	Outside rings divisions	Part Number Type	Year	Indication	Outside rings divisions	Part Number Type	U/Price 1~9
4 years type	12 uniform divisions	DT-R	18 for 2018 Ⓢ Days to ship will be 5-days for the adjustment of production after November 2018. It is scheduled to close sales in April 2019. (available from Sept., 2018)	Month	12 uniform divisions	DTC-R	Quotation
			19 for 2019 (available from Sept., 2018)				
			20 for 2020 (available from Sept., 2019)				
			16 for 2020 (available from Sept., 2019)				
			20 for 2020 (available from Sept., 2019)				
6 years type	12 uniform divisions	DTS-R	18 for 2018 Ⓢ Days to ship will be 5-days for the adjustment of production after November 2018. It is scheduled to close sales in April 2019. (available from Sept., 2018)	Day (1st digit)	10 uniform divisions	DTE-R	Quotation
			19 for 2019 (available from Sept., 2018)				
			20 for 2020 (available from Sept., 2019)				
			16 for 2020 (available from Sept., 2019)				
			20 for 2020 (available from Sept., 2019)				

**Order**

Part Number — Year  
(Year) DT-R16 — 18  
(Month) DTD-R10

**Days to Ship**

Quotation

**Price**

Quotation

Character Designation Type							
Indication							
1M (1 place)	2M (2 places)	3M (3 places)	4M (4 places)	5M (5 places)	6M (6 places)	10M (10 places)	12M (12 places)
Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position

Up to 3 characters can be designated at each engraving position. Up to 2 characters can be designated at each engraving position. Only 1 character can be designated at each engraving position.

Part Number Type	Indication	D	Engraving characters (1~3 characters · Characters printed in blue in indications)												U/Price 1~9					
			Engraving position ①~⑫												1M	2M	3M	4M	5M	6M
DT-R	1M	5	0 1 2 3 4 5 6 7 8 9 A B C D E J F G H I N S T Y K L M P Q R V W X Z												Quotation					
	2M	6																		
	3M	8																		
	4M	10																		
	5M	16																		
	6M	20																		
	10M	20																		

Ⓢ Not applicable to D5 of DT-R5M and DT-R6M. Ⓢ Use ¥ for indicating / (slash), # for — (minus), and % for □ (space).

**Order**

Part Number — ① Characters for engraving — ② Characters for engraving — ③ Characters for engraving — ④ Characters for engraving — ⑤ Characters for engraving — ⑥ Characters for engraving ... — ⑫ Characters for engraving

DT-R 3M 6- POM - PS - SAN  
DT-R 6M 20- JP - US - CN - KR - TH - TW  
DT-R 12M 16- % - 1 - 2 - 3 - 4 - 5 ... - F

**Days to Ship**

Quotation

**Price**

Quotation

**Dividing of outside rings**

1M · 2M · 3M · 4M	12 uniform divisions
6M · 12M	10 uniform divisions
5M · 10M	10 uniform divisions

Date Marked Pins  
Recycle Marked Pins  
Pins with Gas Vent