Note that, for some of the types shown here, order might be unable to be received by the MISUMI Indonesia offices.

Knurled Plastic Knob Screws / Knurled Plastic Handwheels

Knurled

Knurled Plastic Knob Screws - Knurled

Type		Shape	Knob	Screw	
Standard	Stepped		M Material	M Material	S Surface Treatment
NBM	NBLM	Threaded	ABS	SWCH12A	Trivalent Chromate
NBMS	NBLMS	Threaded	ABS	SUS304 Equivalent (SUSXM7)	-
NBF	NBLF	Tapped	ABS	Brass (Insert)	-
NBMR	-	Threaded	Nylon 6	SS400	Trivalent Chromate

A protrusion for demolding is placed under the head.

NBM (Threaded)
NBMR (Threaded)
NBMS (Stainless Steel - Threaded)



NBLM (Threaded)
NBLMS (Stainless Steel - Threaded)



NBF (Tapped)



NBLF (Tapped)



Part Number		L Selection	Knob Color	Lf		H	H1	S	S1	d	d1	Reference Mass (g)			Unit Price					
Type	M (Coarse) - D	NBM, NBLM NBMS, NBLMS		NBF	NBLF							NBM NBLM	NBF NBLF	NBMS NBLMS	NBM	NBF	NBLM	NBLF	NBMS	NBLMS
NBM NBMS NBF Stepped Type NBLM NBLMS NBLF	3-16	10 15	B (Black) W* (White)	5	10	12	16	2	6	11	9	10	5	10						
	4-16	10 15																		
	5-16	10 15 20																		
	5-20	15 20		6	15	14	20.5	4	9.5	15	10	15	6	15						
	5-25	20 25		9	16	18	27	6	15	19		19	9	19						
	6-20	10 15 20		6	15	14	20.5	4	9.5	15		15	6	15						
	6-25	15 20 25		9	16	18	27	6	15	19		29	16	29						
	6-32	20 25								24	12									
	8-32	15 25																		

* White is available for NBM, NBF, NBLM and NBLF only

The default color will be black unless specified.

Knobs Made by Nylon (NBMR)

Part Number		L Selection	Knob Color	H	S	d	d1	Reference Mass (g)	Unit Price
Type	M (Coarse) - D								NBMR
NBMR	5-20	10	B (Black)	14	4	15	10	15	
	6-20	25		14	4	15		15	
	8-25	16 25		18	6	24	12	29	
	8-32	20							

Ordering Example

Part Number	-	L	-	Knob Color
NBM3-16	-	15	-	B
NBM5-20	-	20	-	W
NBMR8-32	-	20	-	B

Knurled Plastic Handwheels

CHBK (Revolving Handle)



CHBKN (Without Handle)



	M Material	S Surface Treatment
Handwheel	Polypropylene	-
Handwheel Insert	Brass	-
Set Screw	SCM435	Black Oxide
Handle	Nylon6 (Black)	-
Handle Thread	SUM22L	Black Oxide

* Tap will be added to the insert (brass).

Part Number		H	A	S	d	R	Lr	h	P	B	G	M	Mass (g)		Unit Price	
Type	D												CHBK	CHBKN	CHBK	CHBKN
CHBK CHBKN	40	20	13	7	18.5	6	15	4	13	13	18.8	4	30	22		
	50	25	17	8	20		19	5	17.5			5	45	37		
	63	29	20	9	23	8	22	6	22	14	20.8		65	58		
	80	36	24	12	28	12	27	6	30	16	23.8	6	97	84		

Ordering Example

Part Number
CHBK40

Knurled Plastic Knob Screws / Knurled Plastic Knob Screws - Large Diameter

Diamond Cut

Knurled Plastic Knob Screws - Diamond Cut

Type		Shape	Knob	Screw	
Standard	Stepped		M Material	M Material	S Surface Treatment
NBMX	NBLMX	Threaded	ABS	SS400	Chrome Plating
NBMSX	NBLMSX	Threaded	ABS	SUS304	-
NBFX	NBLFX	Tapped	ABS	Brass (Insert)	-

A protrusion for demolding is placed under the head.

Standard - Threaded
NBMX (Threaded)
NBMSX (Stainless Steel - Threaded)



Stepped and Threaded
NBLMX (Threaded)
NBLMSX (Stainless Steel - Threaded)



Standard Lever - Tapped
NBFX (Tapped)



Stepped and Tapped
NBLFX (Tapped)



Part Number		L Selection	Lf		H	H1	S	S1	d	d1	Reference Mass (g)			Unit Price					
Type	M (Coarse) - D	NBMX, NBLMX NBMSX, NBLMSX	NBFX	NBLFX							NBMX NBLFX	NBFX NBLMX	NBMSX NBLMSX	NBMX	NBFX	NBLMX	NBLFX	NBMSX	NBLMSX
Standard NBMX NBMSX NBFX Stepped Type NBLMX NBLMSX NBLFX	3-16	10 15	5	10	12	16	2	6	11	9	10	5	10						
	4-16	10 15																	
	5-16	10 15 20																	
	5-20	15 20	6	15	14	22	4	12	15	10	15	6	15						
	5-25	20 25	9	16	18	27	6	15	19		19	9	19						
	6-20	10 15 20	6	15	14	22	4	12	15		15	6	15						
	6-25	15 20 25	9	16	18	27	6	15	19		29	16	29						
	6-32	20 25							24	12									
	8-32	15 25																	

Knurled Plastic Knob Screws - Large Diameter

Type	Shape	Knob	Screw	
		M Material	M Material	S Surface Treatment
NKRM	Threaded	Nylon 6 (Mat Black)	SS400	Trivalent Chromate
NKRF	Tapped	Nylon 6 (Mat Black)	SUM22L	Trivalent Chromate
NKRR	H8 Hole	Nylon 6 (Mat Black)	SS400	Black Oxide

A protrusion for demolding is placed under the head.

(Threaded)
NKRM



(Tapped)
NKRF



(H8 Hole)
NKRR



Threaded, Tapped

Part Number		L Selection	Lf	D	H	S	d	d1	Mass (g)		Unit Price	
Type	M (Coarse)	NKRM	NKRF						NKRM	NKRF	NKRM	NKRF
Threaded NKRM Tapped NKRF	5	10 16 20	10	32	22	10	15	9	13~15	15		
	6	10 16 20 25	15	40	25	11	17	10	20~22	17		
	8	16 20 25	18	50	30	13.5	20	12	36~40	27		
	10	30 40 50	20	63	35	15	23	16	78~90	55		

Part Number		D	Lr	H	S1	S2	d	d1	C	f	Mass (g)	Unit Price
Type	RH8											
H8 Hole NKRR	8	40	15	25	9	11	19	14	2.8	7	31	
	10	50	19	32	13	15.5	22	17	2.8	8	48	
	12	63	23	40	17	20	26	21	3.8	10	89	

Ordering Example

Part Number	-	L
NBMX3-16	-	10
NKRM8	-	16
NKRR12		