

SQUARE SKID BRACKETS / ROUND SKID BRACKETS

SKID BRACKETS WITH SLIDE ADJUSTMENT FUNCTION

RoHS

STB (①+②)
STB-N (① only)

① (Main body)
② (Strut)

Welding
Hexagon nut
Hexagon socket head cap screw M12X25


SS400
Black oxide (Fe₃O₄)

d1	d2	Catalog No.			10mm increments		Base unit price 1 ~ 9 pieces	
		Type	D	L	S	STB	STB-N	
33	33	STB	20					Quotation
45	44	STB-N	32	100~300	0~150			
33	33	STBY	20					
45	44	STBY-N	32					

Order **Catalog No.** - L - S
STB 20 - 100 - 100
STB-N 32 - 40

Days to Ship **Quotation**

Price **Quotation**



RoHS

STBY (①+②)
STBY-N (① only)

① (Main body)
② (Strut)

Welding
Hexagon nut
Hexagon socket head cap screw M12X25

SS400
Black oxide (Fe₃O₄)

RoHS

MRTB (①+②)
MRTB-N (① only)

① (Main body)
② (Strut)

Welding
Hexagon nut M12
Hexagon socket head cap screw M12X25
Key flat

φ D	(A)	B
20	67+S	22.5+S
30	77.5+S	28+S

SS400
Black oxide (Fe₃O₄)

e	d1	d2	Catalog No.			10mm increments		Base unit price 1 ~ 9 pieces	
			Type	D	L	S	MRTB	MRTB-N	
26.0	21	30	MRTB	20				Quotation	
37.5	32	40	MRTB-N	30	100~300	0~150			
26.0	21	30	MRTBY	20					
37.5	32	40	MRTBY-N	30					

Order **Catalog No.** - L - S
MRTB 20 - 100 - 100
MRTB-N 30 - 40

Days to Ship **Quotation**

Price **Quotation**

RoHS

MRTBY (①+②)
MRTBY-N (① only)

① (Main body)
② (Strut)

Welding
Hexagon nut M12
Hexagon socket head cap screw M12X25
Key flat

φ D	(A)	B
20	67+S	22.5+S
30	77.5+S	28+S

SS400
Black oxide (Fe₃O₄)



RoHS

SCTB

Welding
Bolt for slide adjustment
Bolt for shaft tightening

SS400
Black oxide (Fe₃O₄)



RoHS

SCTBY

Welding
Bolt for slide adjustment
Bolt for shaft tightening

SS400
Black oxide (Fe₃O₄)

E	F	D1	Catalog No.		Base unit price 1 ~ 9 pieces	
			Type	D	SCTB	SCTBY
40	15	32	SCTB	20		Quotation
45	20	46	SCTBY	30		

Order **Catalog No.**
SCTB 30

Days to Ship **Quotation**

Price **Quotation**

Alterations **Catalog No.** - (LC)
SCTB 20 - LC100

Alteration	Code	Spec.	1Code
	LC	Reduction of L dimension 80 ≤ LC ≤ 235 5mm increments	Quotation