

Disc Couplings

High Torque, Set Screw

■Features: Couplings with carbon fiber discs have higher torque ratings than the polyimide discs, and are more lateral/angular misalignment tolerant than stainless steel.

Double Disc Type
MCKL (Standard Bore)

MCKLLK (Keywayed Bore d1)
MCKLRK (Keywayed Bore d2)
MCKLWK (Keywayed Bore d1, d2)

Single Disc Type
MCKS (Standard Bore)

MCKSRK (Keywayed Bore d2)
MCKSWK (Keywayed Bore d1, d2)

Standard Bore

	d1 (One Side)	d2 (One Side)	d1, d2 (Both Sides)	Main Body	Disc	Main Body	Accessory
MCKL		MCKLRK	MCKLWK	Aluminum Diecast	Carbon Fiber	Electroless Nickel Plating	Set Screw
MCKS	-	MCKSRK	MCKSWK				

Material

Surface Treatment

Accessory

RoHS 10

The lateral, angular, and axial misalignment values shown are for each occurring individually. When multiple misalignments are occurring simultaneously, the allowable maximum value of each will be reduced to 1/2.

For the selection criteria and alignment procedures, see P1061

Part Number		d1, d2 Selection (d1≤d2)											d3	L	ℓ	F	Set Screw		Unit Price			
Type	D	🔑Keywayed Bore Type is selectable for diameter 6 or larger (D=13 is not available)															M	Tightening Torque (N · m)	MCKL	MCKLLK	MCKLRK	MCKLWK
MCKL MCKLLK MCKLRK MCKLWK	10	2	3	4									4.1	15	4.2	2	M2	0.3			-	-
	13	3	4	5	6							5.5	19	5.5	2.5					-	-	
	16	4	5	6	6.35	7	8						6.8	23.2	7	3	M3	0.7				
	20	4	5	6	6.35	7	8	10				8.1	26	7.5	3.7							
	25	5	6	6.35	7	8	9.53	10	11	12			10.4	30.2	9	4	M4	1.7				
	32	6	6.35	7	8	9.53	10	11	12	14	15	16	15	41	12.4	6						
	40	8	9.53	10	11	12	14	15	16	18	20			19.5	47	15.5			7.8	M5	4	
	50	14	15	16	18	20	22	24	25				25	53	18	9	M6	7				

Part Number		d1, d2 Selection (d1≤d2)											L	ℓ	F	Set Screw		Unit Price				
Type	D	Keywayed Bore Type is selectable for diameter 6 or larger (D=13 is not available)														M	Tightening Torque (N · m)	MCKS	MCKSRK	MCKSWK		
Single Disc Type MCKS MCKSRK MCKSWK	10	2	3	4									10.5	4.2	2	M2	0.3		-	-		
	13	3	4	5	6							13.5	5.5	3				-	-			
	16	4	5	6	6.35	7	8						16.5	7	3	M3	0.7					
	20	4	5	6	6.35	7	8	10				18.4	7.5	4								
	25	5	6	6.35	7	8	9.53	10	11	12				21.6	9	4						
	32	6	6.35	7	8	9.53	10	11	12	14	15	16			29	12.4	6	M4	1.7			
	40	8	9.53	10	11	12	14	15	16	18	20			35	15.5	7.8	M5			4		
	50	14	15	16	18	20	22	24	25					41	18	9	M6	7				

Part Number	Type	D	Allowable Torque (N·m)	Angular Misalignment (°)	Lateral Misalignment (mm)	Static Torsional Spring Constant (N·m/rad)	Max. Rotational Speed (r/min)	Moment of Inertia (kg·m²)	Allowable Axial Misalignment (mm)	Mass (g)
MCKL		10	0.25	2.5	0.2	31	32000	4.6x10 ⁻⁸	±0.2	3
		13	0.35			80	24000	8.0x10 ⁻⁸		5
		16	0.6			130	23000	2.4x10 ⁻⁷	±0.3	9
		20	1.0			220	22000	7.2x10 ⁻⁷		14
		25	2.2			440	19000	2.2x10 ⁻⁶	±0.4	27
		32	3.8			960	15000	6.0x10 ⁻⁶		60
		40	6.8			1900	10000	1.7x10 ⁻⁵	±0.5	104
		50	11.0			2250	8000	4.6x10 ⁻⁵		210

Part Number	Type	D	Allowable Torque (N·m)	Angular Misalignment (°)	Lateral Misalignment (mm)	Static Torsional Spring Constant (N·m/rad)	Max. Rotational Speed (r/min)	Moment of Inertia (kg·m²)	Allowable Axial Misalignment (mm)	Mass (g)
MCKS		10	0.25	1	0.05	40	32000	4.0x10 ⁻⁸		2
		13	0.35			100	24000	7.0x10 ⁻⁸	±0.1	4
		16	0.6			160	23000	2.0x10 ⁻⁷		7
		20	1.0			290	22000	6.0x10 ⁻⁷		11
		25	2.2			550	19000	1.8x10 ⁻⁶		22
		32	3.8			1200	15000	5.2x10 ⁻⁶	±0.2	50
		40	6.8			2200	10000	1.3x10 ⁻⁵		85
		50	11.0			2600	8000	3.6x10 ⁻⁵		170

Part Number	Shaft Bore Dia. d1	Shaft Bore Dia. d2
MCKL20	5	10
MCKLWK25	10	12

Part Number	Shaft Bore Dia. d1	Shaft Bore Dia. d2	Keyway
MCKL20	5	10	RDC6.5
MCKLWK32	10	12	RDC9
			KRH4

Alterations	Shaft Bore Dia.	Keyway Width
Spec.		
	Ordering Code	Ordering Code
	KLH, KRH(b)	KLH, KRH(b)
	Reference Dia. Tolerance	Reference Dia. Tolerance
	8 2 ±0.0125 1.0	8 2 ±0.0125 1.0
	10 4 ±0.0150 1.8	10 4 ±0.0150 1.8
	12 5 ±0.0180 2.3	12 5 ±0.0180 2.3
	22 8 ±0.0180 3.3	22 8 ±0.0180 3.3
	Code	Code
	LDC (Left Shaft) RDC (Right Shaft)	KLH (Left Shaft) KRH (Right Shaft)

Keyway Dimension	Shaft Bore Dia. d1, d2	b	t	Key Nominal Dim. b, t
	6~7.9	2	1.0	2x2
	8~10	3	1.4	3x3
	10.1~12	4	1.8	4x4
	12.1~17	5	2.3	5x5
	17.1~22	6	2.8	6x6
	22.1~25	8	3.3	8x7

Disc Couplings

High Torque, Clamping

■Features: Couplings with carbon fiber discs have higher torque ratings than the polyimide discs, and are more lateral/angular misalignment tolerant than stainless steel.

Double Disc Type
MCKLC (Standard Bore)

MCKLCLK (Keywayed Bore d1)
MCKLCRK (Keywayed Bore d2)
MCKLCWK (Keywayed Bore d1, d2)

Single Disc Type
MCKSC (Standard Bore)

MCKSCWK (Keywayed Bore d1, d2)

Standard Bore

	d1 (One Side)	d2 (One Side)	d1, d2 (Both Sides)	Main Body	Disc	Main Body	Accessory
MCKLC		MCKLCRK	MCKLCWK	Aluminum Diecast	Carbon Fiber	Electroless Nickel Plating	Hex Socket Head Cap Screw
MCKSC	-	MCKSCWK					

Material

Surface Treatment

Accessory

RoHS 10

The lateral, angular, and axial misalignment values shown are for each occurring individually. When multiple misalignments are occurring simultaneously, the allowable maximum value of each will be reduced to 1/2.

For the selection criteria and alignment procedures, see P1061

Part Number		d1, d2 Selection (d1≤d2)							ds	L	ℓ	A	F	Clamp Screw		Unit Price								
Type	D	🔑Keywayed Bore Type is selectable for diameter 6 or larger											M	Tightening Torque (N·m)	MCKLC	MCKLCLK	MCKLCRK	MCKLCWK						
Double Disc Type	13	*3	4	5						5.5	19	5.5	4.1	2.5	M2	0.42		-	-					
	16		*4	5	6					6.8	23.2	7	5	3	M2.5	1								
MCKLC	20		*4	5	6	6.35	7	8		8.1	26	7.5	6.5	3.7										
MCKLCLK	25			*5	6	6.35	7	8	9.53	10	10.4	30.2	9	8.5	4	M3	1.7							
MCKLCRK	32							8	9.53	10	11	12	14		15	41	12.4	10	6	M4	2.5			
MCKLCWK	40							8	9.53	10	11	12	14	15	16	18	19.5	47	15.5	13.1	7.8	M5	7	
	50										14	15	16	18	20	22	24	25	53	18	16.7	9	M6	12

Part Number		d1, d2 Selection (d1≤d2)											L	ℓ	A	F	Clamp Screw		Unit Price				
Type	D	🔑Keywayed Bore Type is selectable for diameter 6 or larger															M	Tightening Torque (N·m)	MCKSC	MCKSCWK			
Single Disc Type MCKSC MCKSCWK	13	*3	4	5									13.5	5.5	4.1	2.5	M2	0.42		-			
	16	*4	5	6									16.5	7	5	3							
	20	*4	5	6	6.35	7	8						18.4	7.5	6.5	3.7	M2.5	1					
	25	*5	6	6.35	7	8	9.53	10					21.6	9	8.5	4	M3	1.7					
	32		8	9.53	10	11	12	14					29	12.4	10	6	M4	2.5					
	40			8	9.53	10	11	12	14	15	16	18			35	15.5	13.1	7.8	M5	7			
	50									14	15	16	18	20	22	24	41	18	16.7	9	M6	12	

When d1 is *3, *4, *5, use with the load torque 50% or less than that shown in the table to prevent slipping.

Part Number	Type	D	Allowable Torque (N·m)	Angular Misalignment (°)	Lateral Misalignment (mm)	Static Torsional Spring Constant (N·m/rad)	Max. Rotational Speed (r/min)	Moment of Inertia (kg·m²)	Allowable Axial Misalignment (mm)	Mass (g)
MCKLC		13	0.35	2.5	0.2	80	12000	8.0x10 ⁻⁸	±0.2	5
		16	0.6			130	9000	2.4x10 ⁻⁷	±0.3	9
		20	0.9			220	7600	7.2x10 ⁻⁷		14
		25	2.2			440	6000	2.2x10 ⁻⁶	±0.4	27
		32	3.8			960	4800	6.0x10 ⁻⁶		60
		40	6.8			1900	4000	1.7x10 ⁻⁵	±0.5	104
		50	11.0			2250	3500	4.6x10 ⁻⁵		210

Part Number	Shaft Bore Dia. d1	Shaft Bore Dia. d2
MCKLC16	5	6
MCKLCWK40	12	15

Part Number	Shaft Bore Dia. d1	Shaft Bore Dia. d2	Keyway
MCKLC20	5	10	RDC6.2
MCKLCWK32	10	12	RDC6.9
			KLH4
			KRH4

Alterations	Shaft Bore Dia.	Keyway Width	Keyway Machining
Spec.			
	Ordering Code	Ordering Code	Ordering Code
	KLH, KRH(b)	KLH, KRH(b)	LK, RK
	Reference Dia. Tolerance	Reference Dia. Tolerance	Reference Dia. Tolerance
	8 2 ±0.0125 1.0	8 2 ±0.0125 1.0	8 2 ±0.0125 1.0
	10 4 ±0.0150 1.8	10 4 ±0.0150 1.8	10 4 ±0.0150 1.8
	12 5 ±0.0180 2.3	12 5 ±0.0180 2.3	12 5 ±0.0180 2.3
	22 8 ±0.0180 3.3	22 8 ±0.0180 3.3	22 8 ±0.0180 3.3
	Code	Code	Code
	LDC (Left Shaft) RDC (Right Shaft)	KLH (Left Shaft) KRH (Right Shaft)	LK (Left Shaft) RK (Right Shaft)

Keyway Dimension	Shaft Bore Dia. d1, d2	b	t	Key Nominal Dim. b, t
	6~7.9	2	1.0	2x2
	8~10	3	1.4	3x3
	10.1~12	4	1.8	4x4
	12.1~17	5	2.3	5x5
	17.1~22	6	2.8	6x6
	22.1~24	8	3.3	8x7