


Roller 28, 38mm Diameter Type


■ **Features:** Short roller conveyors 1m or less, with configurable width and length.




Roller Dia.	Roller Pitch				① Roller (HR028, HR038)		Bearing	② Frame	
	P=30	P=50	P=75	P=100	M Material	S Surface Treatment	M Material	M Material	S Surface Treatment
28mm	ROCOG	ROCOG	-	-	Steel	Trivalent Chromate	Steel	Steel	Trivalent Chromate
38mm	-	ROCOE	ROCOG	ROCOJ					

Roller Dia.	Roller Pitch				R Pin		Frame Coupling Support		Screw, Nut	
	P=30	P=50	P=75	P=100	MMaterial	SSurface Treatment	MMaterial	SSurface Treatment	MMaterial	SSurface Treatment
28mm	ROCOG	ROCOG	-	-	Steel	Trivalent Chromate	Steel	Trivalent Chromate	Steel	Trivalent Chromate
38mm	-	ROCOE	ROCOH	ROCOJ						


Roller Dia.
28mm



Roller Dia
38mm



Roller Conveyor



For Alterations, see P.1170.


For Frame Side View, see P.1166.

■ Roller 28mm Diameter Type

Part Number		(L)		Unit Price										
Type	Number of Rollers	ROCOM P=30	ROCOG P=50	ROCOM (P=30)					ROCOG (P=50)					
				W113	W213	W313	W413	W513	W113	W213	W313	W413	W513	
ROCOM ROCOG	7	(230)	(350)											
	8	(260)	(400)											
	9	(290)	(450)											
	10	(300)	(500)											
	11	(330)	(550)											
	12	(360)	(600)											
	13	(390)	(650)											
	14	(430)	(700)											
	15	(460)	(750)											
	16	(490)	(800)											
	17	(530)	(850)											
	18	(560)	(900)											
	19	(590)	(950)											
	20	(600)	-							-	-	-	-	-
	21	(630)	-							-	-	-	-	-
	22	(660)	-							-	-	-	-	-
	23	(690)	-							-	-	-	-	-
	24	(730)	-							-	-	-	-	-
	25	(760)	-							-	-	-	-	-
	26	(790)	-							-	-	-	-	-
	27	(830)	-							-	-	-	-	-
	28	(860)	-							-	-	-	-	-
	29	(890)	-							-	-	-	-	-
	30	(900)	-							-	-	-	-	-
	31	(930)	-							-	-	-	-	-
	32	(960)	-							-	-	-	-	-

■ Roller 38mm Diameter Type

Part Number		(L)			Unit Price 1 – 5 pc(s).															
Type	Number of Rollers	ROCOE P=50	ROCOH P=75	ROCOJ P=100	ROCOE (P=50)					ROCOH (P=75)					ROCOJ (P=100)					
					W113	W213	W313	W413	W513	W113	W213	W313	W413	W513	W113	W213	W313	W413	W513	
ROCOE ROCOH ROCOJ	4	(200)	(300)	(350)																
	5	(250)	(375)	(450)																
	6	(300)	(475)	(550)																
	7	(350)	(500)	(650)																
	8	(400)	(575)	(750)																
	9	(450)	(675)	(850)																
	10	(500)	(775)	-																
	11	(550)	(800)	-												-	-	-	-	
	12	(600)	(875)	-												-	-	-	-	
	13	(650)	(975)	-												-	-	-	-	
	14	(700)	-	-							-	-	-	-	-	-	-	-	-	
	15	(750)	-	-							-	-	-	-	-	-	-	-	-	
	16	(800)	-	-							-	-	-	-	-	-	-	-	-	
	17	(850)	-	-							-	-	-	-	-	-	-	-	-	
	18	(900)	-	-							-	-	-	-	-	-	-	-	-	
	19	(950)	-	-							-	-	-	-	-	-	-	-	-	



Roller Conveyor Parts Alterations

Stands / Guide Mounts for Roller Conveyors



Alterations

 Part Number - **W** - (SH, GA, GT, KN, ST, SW)

ROCO38	-	113	-	GA-A-L550
ROCO38	-	113	-	KN-G2
ROCOM28	-	113	-	ST-F550
ROCOJ6	-	113	-	GA-A-L550-KN-G2-ST-F550

Alterations	Code	Spec.																
Stand Mounting Hole Machining [Detail]	SH	Roller Conveyors can be hole drilled for stand mounting. Ordering Code SH - SH alteration is applied to ROCOP. - Cannot be combined with ST - Number of Holes for (L) dimension 400 or less is 2, and with the division of center there are 100 Pitches. - Not applicable to (L) dimension 150 or less.																
Conveyor Guide Rails A (Straight) B (One end bent) C (Both ends bent) M Material: Steel S Surface Treatment: Zinc Plating	GA GT	GA : One Conveyor guide is added. GT : Two Conveyor guides are added. Specify L : 100 ~ 1000, in 5mm increment. <table><tr><th>Ordering Code</th><th>Code</th><th>Shape</th><th>Length</th></tr><tr><td>GA</td><td>A</td><td>-</td><td>L300</td></tr><tr><td>GA</td><td>B</td><td>-</td><td>L450</td></tr><tr><td>GA</td><td>C</td><td>-</td><td>L550</td></tr></table> Packaged together with Roller Conveyors.	Ordering Code	Code	Shape	Length	GA	A	-	L300	GA	B	-	L450	GA	C	-	L550
Ordering Code	Code	Shape	Length															
GA	A	-	L300															
GA	B	-	L450															
GA	C	-	L550															
Guide Holder Bracket M Material: Steel S Surface Treatment: Trivalent Chromate	KN	Guide mounting brackets can be added to Roller Conveyors. Ordering Code KN-G2 (Guide Holder Brackets 2pcs.) - Mounting screws and nuts (M10) are included. - The code numerals represent quantities. - Shipped unassembled.																
Conveyor Stand M Material: Steel (SS400) S Surface Treatment: Trivalent Chromate	ST SW	ST : Adds one Roller Conveyor Stand. SW : Adds two Roller Conveyor Stands. Specify F : 450~1200, in 50mm increment. Ordering Code ST-F950 - Applies hole machining on Roller Conveyor when SW is specified. - Shipped unassembled. - Mounting hole location is the same as Alteration SH. - One reinforcement piece for F800 or less.																

M Material	① Mounting Bracket	② Stand	③ Adjusting Bolt	④ Reinforcements
S Surface Treatment	Steel (SS400)			
	Trivalent Chromate			

⚠ Roller Conveyor part alterations are RoHS compliant.

