

Roller Diameter 20mm, 30mm, 50mm Type


■ **Features:** Light weight (approx. 2.3kg/m) Roller Conveyor composed of resin rollers and aluminum frame.



RoHS10

Type	①Roller (HRJA) MMaterial	Bearing MMaterial	②Frame MMaterial SSurface Treatment	
ROCOPI	ABS Plastic	Outer Wheel / Inner Wheel : Polycarbonate Retainer : Nylon 66 Cover : ABS Plastic Ball : SUS304	Aluminum	Clear Anodize

Type	R Pin MMaterial SSurface Treatment		Frame Coupling Support MMaterial SSurface Treatment		Screw, Nut MMaterial SSurface Treatment	
ROCOPI	Steel	Trivalent Chromate	Steel	Trivalent Chromate	Steel	Trivalent Chromate



📍 For Alterations, see **P.1170**. 📍 Rollers are located at both ends of the frame $\frac{P}{2}$. 📍 For Frame Side View, see **P.1166**.

Part Number		Number of Rollers	W (Roller Width)	P (Pitch)	A	D ₁	t	H	Roller Strength for Reference (N)					
Type	D								W113	W213	W313	W413	W513	
ROCOP	20	5-40	113	25	6	9.5	1.5	62	113	105	98	90	83	
	30	5-32		213	40	8	14	1.8	67	162	154	147	139	132
		5-26		313										
	50	5-13	413	75	12	17	2.8	66.5	314	304	294	289	279	
		5-13	513	100										

■ Roller Diameter 20, 30mm Type

Part Number		L			Unit Price 1 ~ 5 pc(s).														
Type	Number of Rollers				W113			W213			W313			W413			W513		
		D20	D30		D20	D30		D20	D30		D20	D30		D20	D30		D20	D30	
		P=25	P=40	P=50	P=25	P=40	P=50	P=25	P=40	P=50	P=25	P=40	P=50	P=25	P=40	P=50	P=25	P=40	P=50
RO COP	5	(120)	(195)	(245)															
	6	(145)	(235)	(295)															
	7	(170)	(275)	(345)															
	8	(195)	(315)	(395)															
	9	(220)	(355)	(445)															
	10	(245)	(395)	(495)															
	11	(270)	(435)	(545)															
	12	(295)	(475)	(595)															
	13	(320)	(515)	(645)															
	14	(345)	(555)	(695)															
	15	(370)	(595)	(745)															
	16	(395)	(635)	(795)															
	17	(420)	(675)	(845)															
	18	(445)	(715)	(895)															
	19	(470)	(755)	(945)															
	20	(495)	(795)	(995)															
	21	(520)	(835)	(1045)															
	22	(545)	(875)	(1095)															
	23	(570)	(915)	(1145)															
	24	(595)	(955)	(1195)															
	25	(620)	(995)	(1245)															
	26	(645)	(1035)	(1295)															
	27	(670)	(1075)	-			-			-			-			-			-
	28	(695)	(1115)	-			-			-			-			-			-
	29	(720)	(1155)	-			-			-			-			-			-
	30	(745)	(1195)	-			-			-			-			-			-
	31	(770)	(1235)	-			-			-			-			-			-
	32	(795)	(1275)	-			-			-			-			-			-
	33	(820)	-	-			-			-			-			-			-
	34	(845)	-	-			-			-			-			-			-
	35	(870)	-	-			-			-			-			-			-
	36	(895)	-	-			-			-			-			-			-
	37	(920)	-	-			-			-			-			-			-
	38	(945)	-	-			-			-			-			-			-
	39	(970)	-	-			-			-			-			-			-
	40	(995)	-	-			-			-			-			-			-

■ Roller Diameter 50mm Type

Part Number		L		Unit Price 1 ~ 5 pc(s).									
Type	Number of Rollers	D50		W113		W213		W313		W413		W513	
		P=75	P=100	P=75	P=100	P=75	P=100	P=75	P=100	P=75	P=100	P=75	P=100
ROCOP	5	(370)	(495)										
	6	(445)	(595)										
	7	(520)	(695)										
	8	(595)	(795)										
	9	(670)	(895)										
	10	(745)	(995)										
	11	(820)	(1095)										
	12	(895)	(1195)										
	13	(970)	(1295)										

📌 For orders larger than indicated quantity, please check with WOS.

! For orders larger than indicated quantity, please check with WOS.




Ordering Example	Part Number	-	Number of Rollers	-	W	-	P
	ROCOP20	-	10	-	213	-	25

Alterations P.1170


Roller 19mm Diameter Type

■ **Features:** Short roller conveyors 1 m or less, with configurable width and length.



RoHS10


Roller Only



For Alterations, see P.1170.

**ROCO
ROCON**

Roller Conveyor



For Frame Side View, see **P.1166**.

Roller Pitch		①Roller (HRO19)		Bearing		②Frame	
P=20	P=30	MMaterial	SSurface Treatment	MMaterial	MMaterial	SSurface Treatment	
ROCO	ROCON	Steel	Trivalent Chromate	Steel	Steel	Trivalent Chromate	

Roller Pitch		R Pin		Frame Coupling Support		Screw, Nut	
P=20	P=30	MMaterial	SSurface Treatment	MMaterial	SSurface Treatment	MMaterial	SSurface Treatment
ROCO	ROCON	Steel	Trivalent Chromate	Steel	Trivalent Chromate	Steel	Trivalent Chromate

Part Number		(L)		Unit Price										
Type	Number of Rollers	ROCO P=20	ROCON P=30	ROCO (P=20)					ROCON (P=30)					
				W113	W213	W313	W413	W513	W113	W213	W313	W413	W513	
ROCO ROCON	6	(120)	(190)											
	7	(140)	(200)											
	8	(160)	(230)											
	9	(180)	(260)											
	10	(200)	(290)											
	11	(220)	(330)											
	12	(240)	(360)											
	13	(260)	(390)											
	14	(280)	(430)											
	15	(300)	(460)											
	16	(320)	(490)											
	17	(340)	(500)											
	18	(360)	(530)											
	19	(380)	(560)											
	20	(400)	(590)											
	21	(420)	(630)											
	22	(440)	(660)											
	23	(460)	(690)											
	24	(480)	(730)											
	25	(500)	(760)											
	26	(520)	(790)											
	27	(540)	(800)											
	28	(560)	(830)											
	29	(580)	(860)											
	30	(600)	(890)											
	31	(620)	(930)											
	32	(640)	-							-	-	-	-	-
	33	(660)	-							-	-	-	-	-
	34	(680)	-							-	-	-	-	-
	35	(700)	-							-	-	-	-	-
	36	(720)	-							-	-	-	-	-
	37	(740)	-							-	-	-	-	-
	38	(760)	-							-	-	-	-	-
	39	(780)	-							-	-	-	-	-
	40	(800)	-							-	-	-	-	-
	41	(820)	-							-	-	-	-	-
	42	(840)	-							-	-	-	-	-
	43	(860)	-							-	-	-	-	-
	44	(880)	-							-	-	-	-	-
	45	(900)	-							-	-	-	-	-
	46	(920)	-							-	-	-	-	-
	47	(940)	-							-	-	-	-	-
	48	(960)	-							-	-	-	-	-



Ordering Example	Part Number	-	W
	ROCO38	-	113
	ROCON22	-	313

Alterations  P.1170