

## Thin Magnetic Catches / Ultrathin Magnetic Catches / Adjustable Magnetic Catches

## Low Dust Generation Magnetic Catches / Low Dust Generation Thin Magnetic Catches / Plastic Catches

**Thin Magnetic Catches** **MGCBU**

RoHS 10

10 pcs. per package. Order quantity should be noted.

Part Name	Material	Surface Treatment
Main Body	ABS Resin	-
Catch Plate	SPCC	Chrome Plating
Magnet	Ferrite	-

Part Number	P	A	t	F	B	P1	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate	
Type	L	1 ~ 9 pkg (s).									10-100
<b>MGCBU</b>	49	34	17	6.5	16.5	24	13	0.9	15		
	59	44	23.5	6.7	23	34	20	2.0	33		
	70	55	24.5	7.7	24	45	30	3.5	49		

10 pcs. per package

**Ultrathin Magnetic Catches** **MGCM**


RoHS 10

There is no catch plate.

Part Name	Material	Surface Treatment
Main Body	SPCC	Nickel Plating
Magnet	Neodymium	Nickel Plating

Part Number	No.	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate	
Type	1 ~ 9 pc (s).					10-100
<b>MGCM</b>	1	1.5	12			
	2	4	12			

Ordering Example **MGCM2**



**Adjustable Magnetic Catches** **AMGCB**


RoHS 10

Part Name	Material	Surface Treatment
Main Body	Polypropylene	-
Catch Plate	SPCC	Chrome Plating
Magnet	Ferrite	-

Part Number	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate		
Type	1 ~ 9 pc (s).				10-19	20-100
<b>AMGCB</b>	1	3.1	15			

**Features** - The magnet position can be adjusted in 5mm increments.

Ordering Example **AMGCB1**



**Low Dust Generation Magnetic Catches** **MGCC**

RoHS 10

No.	Part Name	Material
①	Main Body	Polyacetal
②	Catch Plate	SUS430
③	Magnet	Neodymium Magnet

Part Number	Retention Force (kgf)	Mass (g)	Color	Unit Price	Volume Discount Rate	
Type	1 ~ 9 pc (s).					10-50
<b>MGCC</b>	1	1.0	①Black			
	2	1.4	②Gray			
	3	2.0	③Milky White			
	4	3.3	④White			

Ordering Example **MGCC3**

**Features**

- The magnet encapsulated structure is effective for preventing rust and dust intrusions.
- These magnetic catches are the best suited for use in clean rooms.

Catch Plate is not included for No. 4.

**Low Dust Generation Thin Magnetic Catches** **MGCCU**

RoHS 10

Catch plate is also plastic coated.

Part Name	Material
Main Body	Polyacetal
Catch Plate	SUS430
Magnet	Neodymium Magnet

Part Number	Retention Force (kgf)	Mass (g)	Unit Price	Volume Discount Rate	
Type	1 ~ 9 pc (s).				10-100
<b>MGCCU</b>	1	14			

Ordering Example **MGCCU1**

**Features**

- Catch plate is also plastic coated to reduce particle generation further.

**Plastic Catches** **JMCG**

RoHS 10

Part Name	Material
Female Side	Polyacetal
Male Side	Polyamide

Part Number	Retention Force (kgf)	Latching Force (kgf)	A	B	E	G	H	L	d1	d2	Mass (g)	Color	Unit Price	
Type	1 ~ 50 pcs.													
<b>JMCG</b>	1W	1.7	2.2	26	18	6	24.5	17	2.5	3.3x6	3.3	2	Milky White	
	2B	2.7	3.1	24	17	7	22	15.5	2	2.5x5.5	2.5	1.5	Black	
	2W	2.7	3.1	24	17	7	22	15.5	2	2.5x5.5	2.5	1.5	Milky White	

Ordering Example **JMCG1W**

