
UNI-JOINT PLUGS / HYDRO-CIRCUIT BLOCKS

SPOT COOLING PIPES

-HEAT PROOF TYPE-


Uni-joint plugs



Quotation)-

6

-(()



$\textcircled{\tilde{I}}$ Use in atmospheric pressure 980kPa (10kgf/cm²) or lower.

Characteristics

JWRH

The length can be adjusted within the L \sim L1 range. Heat resistance is 180°C , and it can be used for both cooling water and oil.


50


Notes on handling

Install it in a balanced manner. The structure have allowance of about 1mm in height difference between right and left. However, if it is off balance, excessive load is applied onto the body, which may lead to water leakage.

65

Hydro-circuit blocks





1113

Non JIS material definition is listed on P.1351 - 1352