

# ROLLER CARRIERS / BALL CARRIERS

# EMBOSSED SHOOTER PLATES

**Roller carriers** RoHS **CORO**

① **M** SS400 **M** 55HRC~ (Carburizing)  
② **M** SPCC

Ⓜ (L) dimension is a value for reference only.  
Ⓜ Roller load resistance: 20kg/roller

L	Catalog No.	A Number of rollers	Base unit price 1~9 pieces
(105)	<b>CORO</b>	3	<b>Quotation</b>
(140)		4	
(175)		5	
(210)		6	
(245)		7	
(280)		8	
(315)		9	
(350)		10	
(385)		11	
(420)		12	
(455)		13	
(490)		14	
(525)		15	

L	Catalog No.	A Number of rollers	Base unit price 1~9 pieces
(560)	<b>CORO</b>	16	<b>Quotation</b>
(595)		17	
(630)		18	
(665)		19	
(700)		20	
(735)		21	
(770)		22	
(805)		23	
(840)		24	
(875)		25	
(910)		26	
(945)		27	
(980)		28	

**Ball carriers** RoHS **GORO**

① **M** SUJ2  
②③ **M** SPCC

Ⓜ (L) dimension is a value for reference only.  
Ⓜ Ball load resistance: 8kg/ball

L	Catalog No.	A Number of balls	Base unit price 1~9 pieces
(200)	<b>GORO</b>	4	<b>Quotation</b>
(300)		6	
(400)		8	
(500)		10	
(600)		12	
(700)		14	
(800)		16	
(900)		18	
(1000)		20	
(1100)		22	
(1200)		24	

**Order** **Catalog No.** - **A**  
**CORO** - **10**  
**GORO** - **8**

**Days to Ship** **Quotation**

**P** **Price** **Quotation**

**Ball carriers (individual part)** RoHS **GORON**

①② **M** SUJ2  
③ **M** SUS304  
④ **M** SPCC

Catalog No.	D	D <sub>1</sub>	L	L <sub>1</sub>	H	P	a	d	Load resistance N (kgf)	Weight (g)	Base unit price 1~9 pieces
<b>GORON</b>	41.3	24	10.2	(9.1)	4	30	3.5	15.875	78.4 (8)	45	<b>Quotation</b>

**Order** **Catalog No.**  
**GORON**

**Days to Ship** **Quotation**

**P** **Price** **Quotation**

**Example**  
**CORO**  
**GORO**  
Material

**GORON**  
Conveyor bend point

**EBSP** RoHS

**Surface shape**


**M** SUS304

Catalog No.	A	B	Base unit price
<b>EBSP</b>	500	1000	4,700
	1000	1000	8,000
		2000	15,000

**Order** **Catalog No.** - **A** - **B**  
**EBSP** - **500** - **1000**


**Days to Ship** **Quotation**

**ex** Example



After cutting the plate to the required dimensions, attach it to the scrap shooter by welding or other means.

**Features**



- Because the contact area with scrap is small, this product is suitable for scrap shooters which can only be inclined at a small angle (minimum effective angle: 12 degrees).
- Prevents adhesion caused by lubricating oil.

CONVEYANCE COMPONENTS FOR AUTOMOTIVES